



## pliance®

for horse saddle fitting

# Pressure mapping to optimize saddle fitting

Use **pliance®** to correct **harmful pressure points** that arise from poor saddle fit.

Measure accurately the **dynamic pressure distribution** between saddle and horse using a **thin & elastic** capacitive sensor mat.

### pliance® key benefits for riders:

- detect harmful pressure points using highly accurate and calibrated capacitive sensors
- correct gait asymmetrie and prevent back problems by adapting the saddle and achieving better pressure distribution
- view data immediately with easy-to-use software
- obtain a better understanding of the interaction between rider, saddle and horse



## pliance® application package



The recommended system contains a flexible and elastic measuring mat, a multi-channel analyzer and a software package.

| Technical data     | pliance® saddle mat |
|--------------------|---------------------|
| number of sensors  | 128 (2x)            |
| dimensions (mm)    | 200 x 600 (2x)      |
| sampling rate (Hz) | 60 - 78             |
| pressure range     | 2-60 (standard)     |
| thickness (mm)     | 4.8                 |


## pliance® software features

The pliance® software allows continuous data storage in real-time mode and data handling with a configurable SQL database.

simultaneous video recording

display of calibrated pressure data

peak pressure over time



full access to raw data

force over time

defined areas of interest

loaded area over time

novel GmbH (Global, GER)  
Ismaninger Str. 51, 81675 Munich  
tel: +49 (89) 417767-0  
e-mail: sales@novel.de  
web: www.novel.de

novel electronics inc. (North America)  
3367 Babcock Blvd, Suite 101  
Pittsburgh, PA 15237  
tel: +1 (412) 755-0200  
e-mail: novelinc@novelusa.com  
web: www.novelusa.com